


Rittal – The System.

Faster – better – everywhere.



PK 9515.000

Polykarbonátové skrinky PK

State: 5.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9515.000 - Polykarbonátové skrinky PK bez predvyrazených otvorov

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Features

| | |
|--|---|
| Obj. č. | PK 9515.000 |
| Prevedenie | Rozvádzač PK s nepriehľadným krytom |
| Materiál | Skrinka: polykarbonát spevnený sklenými vláknami Šedý kryt: polykarbonát zosilnený sklenými vláknami, polyuretánové penové tesnenie po celom obvode Skrutky krytu: polyamid Izolačná zátka: polyetylén |
| Farba | RAL 7035 |
| Rozsah dodávky | Skrinka s krytom Skrutky krytu Izolačné upchávky pre skrutky na upevnenie na stenu |
| Protection category NEMA | NEMA 4X |
| Stupeň krytia IP podľa normy EN 60 529 | IP 66 |
| Kód IK | IK08 |

Features

| | |
|-----------------------------|---|
| Rozmery | Šírka: 180 mm Výška: 110 mm Hĺbka: 111 mm |
| Rozsah prevádzkových teplôt | -35 °C...80 °C |
| Základný materiál | Polycarbonate |
| Balenie | 2 pc(s). |
| Netto hmotnosť | 0,84 kg |
| Brutto hmotnosť | 1,04 kg |
| Číslo colnej sadzby | 84879090 |
| ETIM 9 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Popis výrobku | PK polykarbonátová skriňa, ŠxVxH: 180x110x111 mm, polykarbonát zosilnený sklenenými vláknami, bez zoslabených miest na vyrazenie otvorov, so sivým krytom |

Approvals

| | |
|--------------|---------------------------|
| Approvals | C-UL DNV UL |
| Explanations | Declaration of conformity |