

**Rittal – The System.**

Faster – better – everywhere.



**PK 9515.100**

**Polykarbonátové skrinky PK**

State: 28.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9515.100 - Polykarbonátové skrinky PK bez predvyrazených otvorov

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

Obj. č.	PK 9515.100
Prevedenie	Rozvádzač PK s priehľadným krytom
Materiál	Skrinka: polykarbonát spevnený sklenými vláknami Priehľadný kryt: polykarbonát, polyuretánové penové tesnenie po celom obvode Skrutky krytu: polyamid Izolačná zátka: polyetylén
Farba	RAL 7035
Rozsah dodávky	Skrinka s krytom Skrutky krytu Izolačné upchávky pre skrutky na upevnenie na stenu
Protection category NEMA	NEMA 4X
Stupeň krytia IP podľa normy EN 60 529	IP 66
Kód IK	IK08

## Features

Rozmery	Šírka: 180 mm Výška: 110 mm Hĺbka: 111 mm
Rozsah prevádzkových teplôt	-35 °C...80 °C
Základný materiál	Polycarbonate
Balenie	2 pc(s).
Netto hmotnosť	0,804 kg
Brutto hmotnosť	1,003 kg
Číslo colnej sadzby	84879090
ETIM 9	EC000261
ECLASS 8.0	27180101
Popis výrobku	PK polykarbonátová skriňa, ŠxVxH: 180x110x111 mm, polykarbonát zosilnený sklenenými vláknami, bez zoslabených miest na vyrazenie otvorov, s priehľadným krytom

## Approvals

Approvals	C-UL DNV UL
Explanations	Declaration of conformity