

Rittal – The System.

Faster – better – everywhere.



PK 9519.000

Polykarbonátové skrinky PK

State: 1.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9519.000 - Polykarbonátové skrinky PK bez predvyrazených otvorov

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Features

Obj. č.	PK 9519.000
Prevedenie	Rozvádzač PK s nepriehľadným krytom
Materiál	Skrinka: polykarbonát spevnený sklenými vláknami Šedý kryt: polykarbonát zosilnený sklenými vláknami, polyuretánové penové tesnenie po celom obvode Skrutky krytu: polyamid Izolačná zátka: polyetylén
Farba	RAL 7035
Rozsah dodávky	Skrinka s krytom Skrutky krytu Izolačné upchávky pre skrutky na upevnenie na stenu
Protection category NEMA	NEMA 4X
Stupeň krytia IP podľa normy EN 60 529	IP 66
Kód IK	IK08

Features

Rozmery	Šírka: 182 mm Výška: 180 mm Hĺbka: 165 mm
Rozsah prevádzkových teplôt	-35 °C...80 °C
Základný materiál	Polycarbonate
Balenie	1 pc(s).
Netto hmotnosť	0,841 kg
Brutto hmotnosť	0,941 kg
Číslo colnej sadzby	84879090
ETIM 9	EC000261
ECLASS 8.0	27180101
Popis výrobku	PK polykarbonátová skriňa, ŠxVxH: 182x180x165 mm, polykarbonát zosilnený sklenenými vláknami, bez zoslabených miest na vyrazenie otvorov, so sivým krytom

Approvals

Approvals	C-UL DNV UL
Explanations	Declaration of conformity