

Rittal – The System.

Faster – better – everywhere.



SV 9677.915 Pripojovacie bloky

State: 18.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.915 - Pripojovacie bloky

For connecting cables and laminated copper bars.

Features

Obj. č.	SV 9677.915
Materiál	Oceľový plech, pozinkovaný E-Cu, pocínované
Vývod vodičov	Top/bottom
Spôsob (elektrického) pripojenia	Box terminal
Menovitý prúd max.	1 000 A
Rozmery	Šírka: 98 mm
Pripojenie okrúhlych vodičov	185 - 300 mm ²
Vhodné pre prípojnice	Výška: 10 mm
Balenie	1 pc(s).
Netto hmotnosť	1,2 kg
Brutto hmotnosť	1,35 kg
Podiel medi (kg / ks)	0,893
PCF per pack (cradle-to-gate)	5,1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	85369095
ETIM 9	EC002270
ECLASS 8.0	27400613
Popis výrobku	Pripojovací blok SV, 1000 A, 690 V, 1-pólový, káblový vývod hore/ dole, pripojenie okrúhleho vodiča 185-300 mm ²

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK
