

Rittal – The System.

Faster – better – everywhere.



SV 9677.920 Pripojovacie bloky

State: 22.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.920 - Pripojovacie bloky

For connecting cables and laminated copper bars.

Features

Obj. č.	SV 9677.920
Materiál	Oceľový plech, pozinkovaný E-Cu, pocínované
Vývod vodičov	Top/bottom
Spôsob (elektrického) pripojenia	Ring terminal M12
Menovitý prúd max.	1 600 A
Rozmery	Šírka: 98 mm
Pripojenie okrúhlych vodičov	240 mm ²
Vhodné pre prípojnice	Výška: 10 mm
Balenie	1 pc(s).
Netto hmotnosť	1,6 kg
Brutto hmotnosť	1,662 kg
Podiel medi (kg / ks)	1,471
PCF per pack (cradle-to-gate)	6,3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	85369095
ETIM 9	EC002270
ECLASS 8.0	27400613
Popis výrobku	Pripojovací blok SV, 1600 A, 690 V, 1-pólový, horný/dolný vývod kábla, pripojenie okrúhleho vodiča 240 mm ²

Approvals

Approvals

UL + C-UL (listed)

Explanations

Declaration of conformity

Declaration of conformity UK