

Rittal – The System.

Faster – better – everywhere.



SV 9682.163 Delené dvere

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9682.163 - Delené dvere pre VX

Door may be optionally hinged on the right or left.

Features

Obj. č.	SV 9682.163
Materiál	Oceľový plech, 2 mm
Povrch	Štruktúrovaný náter
Farba	RAL 7035
Rozsah dodávky	Delené dvere Deliaca priečka Pánty Uzatváracie diely Vrátane upevňovacieho materiálu
Poznámka	Uhol otvorenia delených dverí max. 130°
Uzáver	Počet uzáverov: 1
Rozmery	Šírka: 600 mm Výška: 300 mm
Vhodné pre	Šírka: = 600 mm
Stupeň krytia IP podľa normy IEC 60 529	IP 54
Balenie	1 pc(s).
Netto hmotnosť	4,1 kg
Brutto hmotnosť	4,5 kg
PCF per pack (cradle-to-gate)	17,1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	94039910
ETIM 9	EC000747
ECLASS 8.0	27182204

Features

Popis výrobku

SV čiastkové dvere pre VX, ŠxV: 600x300 mm

Approvals

Approvals

DNV
Lloyds Register
UL + C-UL (listed)
UL + C-UL - FTFA

Explanations

Declaration of conformity UK