



Rittal – The System.

Faster – better – everywhere.



SV 9682.190 Delené dvere

State: 22.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9682.190 - Delené dvere pre VX

Door may be optionally hinged on the right or left.

Features

Obj. č.	SV 9682.190
Materiál	Oceľový plech, 2 mm
Povrch	Štruktúrovaný náter
Farba	RAL 7035
Rozsah dodávky	Delené dvere Deliaca priečka Pánty Uzatváracie diely Vrátane upevňovacieho materiálu
Poznámka	Uhol otvorenia delených dverí max. 130°
Uzáver	Počet uzáverov: 4
Rozmery	Šírka: 800 mm Výška: 2.000 mm
Vhodné pre	Šírka: = 800 mm
Stupeň krytia IP podľa normy IEC 60 529	IP 54
Balenie	1 pc(s).
Netto hmotnosť	33 kg
Brutto hmotnosť	33,5 kg
PCF per pack (cradle-to-gate)	127,6 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	94039910
ETIM 9	EC000747
ECLASS 8.0	27182204

Features

Popis výrobku

SV čiastkové dvere pre VX, ŠxV: 800x2000 mm

Approvals

Approvals

UL + C-UL (listed)

UL + C-UL - FTTA

Explanations

Declaration of conformity UK