

# Rittal – The System.

Faster – better – everywhere.



## SV 9690.033 Energy storage frame

State: 21.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9690.033 - Energy storage frame VX ESS

Enclosure frame with flexible interior fit-out. Ideal for efficient and modular energy storage installation.

## Features

Obj. č.	SV 9690.033
Materiál	Rámová konštrukcia skrine: oceľový plech, 1,5 mm Montážne uhly: oceľový plech, 2 mm Cross-member with mounting angle: Sheet steel, 3 mm
Povrch	Rámová konštrukcia skrine: základná farba nanosená máčaním Profilové lišty: pozinkované Cross-member with mounting bracket: Zinc-plated
Farba	RAL 7035
Rozsah dodávky	Rámová konštrukcia skrine
Rozmery	Šírka: 800 mm Výška: 2.000 mm Hĺbka: 800 mm
Balenie	1 pc(s).
Netto hmotnosť	54 kg
Brutto hmotnosť	54,8 kg
PCF per pack (cradle-to-gate)	137,31 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	94032080
ETIM 9	EC000261
Popis výrobku	VX ESS energy storage frame WxHxD: 800x2000x800 mm, with interior fit-out