

# Rittal – The System.

Faster – better – everywhere.



## IT 5302.042

## 19 英寸电缆桥架，可调深度

状态: 2026/2/11 (来源: [ittal.com/tw-zh](https://www.ittal.com/tw-zh))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# IT 5302.042 - 19 英寸电缆桥架，可调深度

Within the 482.6 mm (19") mounting level, the cable link provides an integrated cable routing option between the front and rear mounting levels inside an enclosure.

## 特征

型号	IT 5302.042
您的收益	<p>Cable entry at the front via brush strip for thermal partitioning of the cable entry zone</p> <p>Direct cable routing between the patch level and component with rear installation, optimum cable routing with switch mounted at the rear</p> <p>Fully depth-variable with versatile, infinitely adjustable extension of the cable link</p> <p>Prevents incorrect airflow by partitioning the transition</p> <p>Open at the top for easy retrofitting, even with cables already inserted</p> <p>Cable link extendable upwards by 1 U, by using an additional cable entry panel with brush strip</p>
材料	<p>钢板</p> <p>刷条：塑料，符合 UL 94-V0</p>
表面	喷漆
颜色	RAL 9005
供货范围	<p>Cable link</p> <p>刷条</p>
安装可能性	用于固定前后 19" 的安装平面
层面间距	500 - 750 mm
高度单位	1 U

# 特征

承载力 (静态)	150 N
适用于	用于不受机柜影响的独立安装
说明	Assembly parts should be ordered separately
包装单元	1 件
本型号 (含包装) PCF (出厂前)	PCF-Wert 18,78 kg Co <sup>2</sup> e
税率号	73269098