

Rittal – The System.

Faster – better – everywhere.



SV 9393.567

电流互感器

状态: 2025/7/15 (来源: rittal.com/tw-zh)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9393.567 - 电流互感器

特征

型号	SV 9393.567
型式	Output voltage 333 mV
材料	聚酰胺 防火性能根据 UL 94
颜色	RAL 9005
供货范围	2 个插接底脚 4 insulating caps 2 个主母线端子 4 颗螺纹销钉
适合于母线	2 x 80 x 10 60 x 60
Primary current	1,250 A
标准	DIN EN 61869-1/2 EN 42600 VDE 0100 DIN EN 50274/VDE 0660-514 DGUV V3 规范
尺寸	宽度: 105 mm 高度: 132 mm 深度: 30 mm
工作温度范围	-5 °C...55 °C
贮存温度范围	-25 °C...75 °C
空气湿度 (没有凝露)	10...90 %

特征

基波频率	50...60 Hz
Accuracy Class	0.5
Insulation material (class)	F
包装单元	1 件
净重	0.435
毛重	0.444
税率号	85043129
EAN	4028177049772
ETIM 9	EC002048

批准

解释	符合性声明
----	-------