

# Rittal – The System.

Faster – better – everywhere.



## SV 9393.572

## 电流互感器

状态: 2025/7/15 (来源: [rittal.com/tw-zh](http://rittal.com/tw-zh))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9393.572 - 电流互感器

## 特征

型号	SV 9393.572
型式	Output voltage 333 mV
材料	聚酰胺 防火性能根据 UL 94
颜色	RAL 9005
供货范围	2 个插接底脚 4 insulating caps 2 个主母线端子 4 颗螺纹销钉
适合于母线	2 x 100 x 10 80 x 60 50 x 80
Primary current	2,500 A
标准	DIN EN 61869-1/2 EN 42600 VDE 0100 DIN EN 50274/VDE 0660-514 DGUV V3 规范
尺寸	宽度: 129 mm 高度: 156 mm 深度: 30 mm
工作温度范围	-5 °C...55 °C
贮存温度范围	-25 °C...75 °C

## 特征

---

空气湿度 (没有凝露)	10...90 %
基波频率	50...60 Hz
Accuracy Class	0.5
Insulation material (class)	F
包装单元	1 件
净重	0.55
毛重	0.558
税率号	85043129
EAN	4028177049925
ETIM 9	EC002048

## 批准

---

解释 符合性声明