

**Rittal – The System.**

Faster – better – everywhere.



# KL 1529.010

## Terminal boxes KL

State: 11.05.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KL 1529.010 - Terminal boxes KL Stainless steel

Terminal boxes, stainless steel 1.4301 (AISI 304), Protection category IP 66.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | KL 1529.010   |
| Material                          | Enclosure: Stainless steel 1.4301 (AISI 304)<br>Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal |
| Surface finish                    | Enclosure and cover: Brushed, grain 180   |
| Supply includes                   | Enclosure with cover<br>Quick-release fastener including plastic bushes   |
| Protection category NEMA          | NEMA 4X   |
| Protection category to IEC 60 529 | IP 66   |
| IK Code                           | IK08  |
| Dimensions                        | Width: 300 mm<br>Height: 200 mm<br>Depth: 120 mm  |
| Material thickness - cover        | 1.25 mm   |
| Material thickness - enclosure    | 1.25 mm   |
| Lock                              | Number of locks: 4  |
| Basic material                    | Stainless steel 1.4301 (AISI 304)   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 2.7 kg  |
| Gross weight                      | 2.975 kg  |
| Customs tariff number             | 84879090  |
| ETIM 9                            | EC000261  |
| ETIM 8                            | EC000261  |
| ECLASS 8.0                        | 27180101  |

# Features

---

|                     |   |
|---------------------|---|
| Product description | KL Terminal box, WHD: 300x200x120 mm, Stainless steel 1.4301, without mounting plate, with cover, without gland plate |
|---------------------|---|

# Approvals

---

|           |   |
|-----------|---|
| Approvals | Bureau Veritas<br>DNV<br>UL + C-UL (listed) |
|-----------|---|

---

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|