

Rittal – The System.

Faster – better – everywhere.



KL 1581.000

Plastic cable gland plates

State: 06.04.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1581.000 - Plastic cable gland plates with PG knockouts

With pre-punched PG holes for cable glands.



Features

| | |
|-----------------------------------|---|
| Model No. | KL 1581.000 |
| Product description | With pre-punched PG holes for cable glands. Use seal for standard gland plates. |
| Material | ABS |
| Colour | RAL 7035 |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures |
| No. of metric knockouts | 12 |
| Number x PG diameter | 12 x 13.5 |
| Dimensions | Width: 220 mm Depth: 90 mm |
| To fit | Enclosure type: KL |
| Gland plate | Size: 2 |
| Operating temperature range | -40 °C...70 °C |
| Protection category to IEC 60 529 | IP 55 if installed correctly |
| Packs of | 5 pc(s). |
| Net weight | 0.505 kg |

Features

| | |
|-----------------------|--|
| Gross weight | 0.604 kg |
| Customs tariff number | 73079100 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |
| Product description | KL Plastic cable gland plate, with PG knock-outs, WD: 220x90 mm, size: 2, PG knockouts: 13.5 |