

Rittal – The System.

Faster – better – everywhere.



SZ 1581.200

Metal gland plate

State: 24.08.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 1581.200 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands using a screwdriver, IP 66 when mounting in the usual position at the bottom.

Features

| | |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------|
| Model No. | SZ 1581.200 |
| Product description | Simply knock out the holes for the cable glands using a screwdriver. |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures |
| No. of metric knockouts | 12 x M20 |
| Dimensions | Width: 220 mm Depth: 90 mm |
| To fit | Enclosure type: KX |
| Protection category to IEC 60 529 | IP 55 if installed correctly |
| Type rating to UL 50E | Type 1 Type 12K |
| Number knockouts | 12 |
| Metric diameter | M20 |
| Packs of | 1 pc(s). |
| Net weight | 0.23 |
| Gross weight | 0.24 |
| PCF per pack (cradle-to-gate) | 1.2 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73079100 |
| EAN | 4028177940536 |

Features

| | |
|-----------------|----------|
| E-Number Sweden | E3465317 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|