

Rittal – The System.

Faster – better – everywhere.



SG 2376.020

Acoustic component

State: 23.08.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2376.020 - Acoustic component for signal pillar, modular

To indicate warnings or malfunctions.

Features

Model No.	SG 2376.020
Design	Continuous tone or pulsating, 85 dB, max. 25 mA
Product description	To indicate warnings or malfunctions.
Benefits	Simple assembly and contact via bayonet fastener.
Applications	Mounting only on the upper end of the optical components or directly on the connection component.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel
Material	Enclosure of polyamide
Colour	Black
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Packs of	1 pc(s).
Net weight	0.09
Gross weight	0.106
Customs tariff number	85311095
EAN	4028177220454
ECLASS 8.0	27371237

Approvals

Approvals

Approvals

UR