

Rittal – The System.

Faster – better – everywhere.



SG 2376.030

Acoustic component

State: 06.04.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2376.030 - Acoustic component for signal pillar, modular

To indicate warnings or malfunctions.

Features

Model No.	SG 2376.030
Design	Volume and 8 tones may be set, 100 dB, max. 25 mA
Product description	To indicate warnings or malfunctions.
Benefits	Simple assembly and contact via bayonet fastener.
Applications	Mounting only on the upper end of the optical components or directly on the connection component.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel
Material	Enclosure of polyamide
Colour	Black
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Packs of	1 pc(s).
Net weight	0.11 kg
Gross weight	0.112 kg
Customs tariff number	85369095
ECLASS 8.0	27371237
Product description	SG Acoustic component, for signal pillar, modular, 230 V, 100 dB, max. 25 mA

Approvals

Approvals

UR