


# Rittal – The System.

Faster – better – everywhere.



## AE 2383.300 Rail for interior installation

State: 06.04.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 2383.300 - Rail for interior installation for AE/WM

For mounting in the enclosure, no machining required. Suitable for all-round mounting on the sides, base and roof areas.



## Features

Model No.	AE 2383.300
Product description	For mounting in the enclosure, no machining required. Suitable for all-round mounting on the sides, base and roof areas. Variable with 2 rows of system punchings, creates additional mounting space e.g. for: TS punched section, enclosure lights, door-operated switch, door stay, cable conduit holder
Material	Sheet steel
Surface finish	Zinc-plated
Note	Other mounting options: Mounting plates, locatable, TS 8612.400 Mounting plates, screw-fastening, large, TS 8612.410 Mounting plates, screw-fastening, small, PS 4532.000 Mounting bracket, PS 4597.000
To fit	Enclosure type: AE Depth: = 300 mm
Packs of	4 pc(s).
Net weight	0.8 kg
Gross weight	0.92 kg
Customs tariff number	73269098
ETIM 9	EC002625
ETIM 8	EC002625

# Features

---

ECLASS 8.0

27189234

---

Product description

AE Rail for interior installation, for AE, for D: 300 mm