


Rittal – The System.

Faster – better – everywhere.



AX 2394.100

Base configuration rail

State: 23.08.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2394.100 - Base configuration rail for AX

Rail for flexible interior configuration of AX compact enclosures in combination with the new AX rail for interior installation. For mounting e.g. VX punched section with mounting flange 23 x 64 mm, LED system lights, VX cable clamp rails and support rails.



Features

Model No.	AX 2394.100
Product description	For mounting in the enclosure depth, on the existing threaded bolts, no machining required. System punchings on 2 sides. Creates additional installation options.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Length	99 mm
Installation options	For installation in AX sheet steel, only in conjunction with rail for interior installation AX
To fit	Enclosure type: AX
Packs of	4 pc(s).
Net weight	0.4
Gross weight	0.451
PCF per pack (cradle-to-gate)	1.6 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098

Features

EAN	4028177965737
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189234