

**Rittal – The System.**

Faster – better – everywhere.



# HD 2410.000

## Cable gland HD

State: 23.05.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 2410.000 - Cable gland HD

HD cable gland IP 68 (5 bar, 30 min.)



## Features

Model No.	HD 2410.000
Design	Standard
Benefits	Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Manufacturer Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303) Seal: Conforms to FDA 21 CFR 177.2600
Dimensions	Thread: M12 x 1.5
For cable diameters	3 - 6.5 mm
Operating temperature range	-20 °C...100 °C

# Features

---

IP protection category to IEC 60529	IP 68 (5 bar, 30 min)
Packs of	5 pc(s).
Net weight	0.115 kg
Gross weight	0.123 kg
Customs tariff number	73181900
ECLASS 8.0	27149109
Product description	HD Cable gland, stainless steel 1.4305, size: M12x1,5, for cables Ø 3-6.5 mm, Standard version

# Approvals

---

Explanations	Manufacturer's declaration
--------------	----------------------------