

Rittal – The System.

Faster – better – everywhere.



SZ 2561.010

Plastic cable gland plates

State: 23.05.2026 (Source: rittal.com, ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2561.010 - Plastic cable gland plates with metric knockouts

With pre-punched holes for cable glands.

Features

| | |
|-----------------------------------|--|
| Model No. | SZ 2561.010 |
| Product description | With pre-punched holes for cable glands. Use seal for standard gland plates. |
| Colour | RAL 7035 |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures |
| No. of metric knockouts | 3 x M16 5 x M20 4 x M25 2 x M32 2 x M40 |
| Dimensions | Width: 330 mm Depth: 90 mm |
| To fit | Enclosure type: AE |
| Gland plate | Size: 3 |
| Operating temperature range | -40 °C...70 °C |
| Protection category to IEC 60 529 | IP 55 if installed correctly |
| Packs of | 10 pc(s). |
| Net weight | 1.13 kg |
| Gross weight | 1.396 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |

Features

Product description

SZ Plastic cable gland plate, with metric knock-outs, WD: 330x90 mm, size: 3