

Rittal – The System.

Faster – better – everywhere.



SZ 2563.100

Metal gland plate

State: 04.11.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2563.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands using a screwdriver, IP 66 when mounting in the usual position at the bottom.

Features

Model No.	SZ 2563.100
Product description	Simply knock out the holes for the cable glands using a screwdriver.
Material	Sheet steel
Colour	RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	1 x M12 12 x M20 11 x M25 8 x M32 4 x M40
Dimensions	Width: 534 mm Depth: 149 mm
To fit	Enclosure type: AE
Gland plate	Size: 5
Protection category to IEC 60 529	IP 66 when mounting in the usual position at the bottom
Number knockouts	1 12 11 8 4
Metric diameter	M12 M20 M25 M32 M40
Packs of	1 pc(s).

Features

Net weight	0.96
Gross weight	1.004
Customs tariff number	73079100
EAN	4028177390874
E-Number Sweden	E3404797
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421