

Rittal – The System.

Faster – better – everywhere.



FT 2761.010 Viewing window

State: 08.07.2026 (Source: [rittal.com/ua-en](https://www.rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2761.010 - Viewing window for AX

For external mounting on AX enclosures instead of a door and on surfaces.



Features

| | |
|-----------------------------------|---------------------------------------------------------------------------|
| Model No. | FT 2761.010 |
| Design | 60 section |
| Product description | For external mounting on AX enclosures instead of a door and on surfaces. |
| Material | Frame: Aluminium, natural anodised. Glass panel: Acrylic |
| Supply includes | Plastic handle with lock insert no. 3524 E |
| Protection category to IEC 60 529 | IP 54 |
| To fit Model No. | 1010.000 1054.000 1060.000 1360.000 |
| To fit | Enclosure type: AX Width: = 600 mm Height: = 600 mm |
| Dimensions | Width: 597 mm Height: 597 mm Depth: 62 mm |

Features

| | |
|-----------------------------------|-------------------------------------------------------------------------------------------|
| Visible area | Viewing window width: 537 mm Viewing window height: 537 mm |
| Build depth for components (max.) | 58 mm |
| Packs of | 1 pc(s). |
| Net weight | 4.061 kg |
| Gross weight | 4.18 kg |
| Customs tariff number | 76101000 |
| ETIM 9 | EC002527 |
| ETIM 8 | EC002527 |
| ECLASS 8.0 | 27182204 |
| Product description | FT Viewing window, WHD: 597x597x62 mm, for AX enclosures instead of the door and surfaces |