

Rittal – The System.

Faster – better – everywhere.



SV 3057.000 Busbar support

State: 22.05.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3057.000 - Busbar support

For busbar systems 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm).



Features

| | |
|-----------------------|---------------------------------------------------------------------------------------------------|
| Model No. | SV 3057.000 |
| Material | Fibreglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Number of poles | 3-pole 150 mm |
| To fit busbars | 60 x 10 80 x 10 100 x 10 |
| Rated current max. | 3,000 A |
| Dimensions | Width: 30 mm Height: 420 mm Depth: 170 mm |
| Packs of | 2 pc(s). |
| Net weight | 4.496 kg |
| Gross weight | 4.695 kg |
| Customs tariff number | 85469010 |
| ETIM 9 | EC001166 |
| ETIM 8 | EC001166 |
| ECLASS 8.0 | 27400607 |

Features

Product description

SV Busbar support, 3-pole, 150 mm bar centre distance, for busbar
WH: 100x10 mm

Approvals

Explanations

Declaration of conformity
Declaration of conformity UK

Tender text

SV busbar support
for accommodating busbars. Suitable for busbars
3 x 2 x 100 x 10 mm.

Rated operating voltage: 1000 V~, 50/60 Hz
to VDE 0660

Rated current: up to 3000 A

Material: PBT

Fire protection: UL 94-V0

Continuous operating temperature: 140 °C

Bar centre distance: 150 mm

Tightening torques

Assembly screws: 8 - 10 Nm

Lid attachment: 5 - 10 Nm