


# Rittal – The System.

Faster – better – everywhere.



## SK 3164.230

### Roof-mounted fans

State: 06.07.2025 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3164.230 - Roof-mounted fans for VX, VX IT

Roof-mounted fan for the office sector with exceptionally low noise level (40 dB) and high volumetric flow (unimpeded air flow 1500 m<sup>3</sup>/h).



## Features

Model No.	SK 3164.230
Benefits	Easy assembly, the roof plate variant eliminates the need to create mounting cut-outs Fully wired ready for connection
Material	Sheet steel, spray-finished
Colour	RAL 7035
Supply includes	Roof-mounted fans Assembly parts
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 0.3 A At 60 Hz: 0.35 A
Dimensions	Width: 511 mm Height: 227 mm Depth: 511 mm
IP protection category to IEC 60 529	Internal circuit IP 54
Note	Reduction in the specified air throughput to 800 m <sup>3</sup> /h at 40 Pa counterpressure using two vented base/plinth trim panels
Operating temperature range	20 °C...55 °C
Packs of	1 pc(s).

# Features

Net weight	18.35
Gross weight	19.36
Customs tariff number	84145915
EAN	4028177309494
ECLASS 8.0	27180716

# Approvals

Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK