

Rittal – The System.

Faster – better – everywhere.



SK 3172.100 Chopped-fibre filter mat

State: 10.05.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3172.100 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

Features

Model No.	SK 3172.100
Design	for filter fans
Product description	Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Chemical fibres
Note	No suitable for use in EMC filter fans.
To fit Model No.	3240.... 3241....
Dimensions	Width: 221 mm Height: 221 mm Depth: 17 mm
Filter class	to DIN EN 779: G3 to DIN EN ISO 16890: ISO Coarse 50%
Packs of	5 pc(s).
Net weight	0.095 kg
Gross weight	0.1 kg
Customs tariff number	56039390
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Product description	SK spare filter mats, for filter fans, for SK 3240.../3241..., WHD: 221 x 221 x 17 mm

Approvals

Approvals

UR + C-UR (recognized)