Rittal – The System.

Faster – better – everywhere.





SK 3173.105 Chopped-fibre filter mat

State: 04.11.2025 (Source: rittal.com/ua-en)



SK 3173.105 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

Features

Model No.	SK 3173.105
Design	for filter fans
Product description	Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 μm.
Material	Chemical fibres
Note	No suitable for use in EMC filter fans.
To fit Model No.	3243 3244 3245
Dimensions	Width: 289 mm Height: 289 mm Depth: 17 mm
Filter class	to DIN EN 779: G3 to DIN EN ISO 16890: ISO Coarse 50%
Packs of	50 pc(s).
Net weight	1.2
Gross weight	1.72
Customs tariff number	56039390
EAN	4028177695573
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

© Rittal 2025 2

Approvals

Approvals	UR + C-UR (recognized)
Certificates	EAC

© Rittal 2025 3