

Rittal – The System.

Faster – better – everywhere.



SK 3236.124

Mini fan

State: 25.06.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3236.124 - Mini fan

Compact DC fan for enclosure and component cooling in enclosures.

Features

Model No.	SK 3236.124
Product description	Compact DC fan for enclosure and component cooling in enclosures.
Supply includes	Fan Assembly screws Contact hazard protection
Rated operating voltage	24 V (DC)
Power consumption Pel	With DC: 1 W
Dimensions	Width: 60 mm Height: 60 mm Depth: 25.4 mm
Note	Electrical connection via 2 single wires (length approx. 300 mm)
Operating temperature range	-20 °C...70 °C
Noise level	With DC: 20 dB(A)
Packs of	1 pc(s).
Net weight	0.11 kg
Gross weight	0.12 kg
Customs tariff number	84145915
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716
Product description	SK Mini fan, 1 W, 24 V (DC), WHD: 60 x 60 x 25.4 mm

Approvals

Approvals

UR

Explanations

Declaration of conformity