Rittal – The System.

Faster – better – everywhere.





SK 3237.055 Chopped-fibre filter mat

State: 27.10.2025 (Source: rittal.com/ua-en)



SK 3237.055 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

Features

| Model No. | SK 3237.055 |
|-----------------------|--|
| Design | for filter fans |
| Product description | Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 μm. |
| Material | Chemical fibres |
| Colour | White |
| Note | No suitable for use in EMC filter fans. |
| To fit Model No. | 3237.3xx/3237.7xx |
| Dimensions | Width: 89 mm Height: 89 mm Depth: 10 mm |
| Filter class | to DIN EN 779: G2 to DIN EN ISO 16890: ISO Coarse 50% |
| Packs of | 50 pc(s). |
| Net weight | 0.05 |
| Gross weight | 0.164 |
| Customs tariff number | 56039390 |
| EAN | 4028177651548 |
| ETIM 9 | EC002513 |
| ETIM 8 | EC002513 |
| ECLASS 8.0 | 27180706 |

© Rittal 2025 2

Approvals

| Approvals | UR + C-UR (recognized) |
|--------------|------------------------|
| Certificates | EAC |

© Rittal 2025 3