


Rittal – The System.

Faster – better – everywhere.



SK 3285.940 Pleated filter

State: 19.04.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3285.940 - Pleated filter for fan-and-filter units, roof-mounted fans, cooling units and chillers

The high-quality pleated filter technology permits a significant increase in the volumetric air flow compared to conventional chopped-fibre filter mats. Cooling unit performance is improved and energy consumption is lower. The enhanced filtration properties also mean less dust in the enclosure or unit, and the resulting longer maintenance intervals reduce service costs significantly.

Features

Model No.	SK 3285.940
Design	for chillers
Material	Polyester
Note	Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
To fit Model No.	3319.100 3320.200 3334.300 3334.360 3334.440 3334.460 3334.470 3334.480 3334.400 3334.450
Dimensions	Width: 131 mm Height: 113 mm Depth: 13 mm
Filter class	to DIN EN 779: G3
Packs of	3 pc(s).
Net weight	0.087 kg
Gross weight	0.097 kg

Features

Customs tariff number	56039390
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Product description	SK Pleated filter Blue e+ chillers (inverter housings) 3320.200/3334.300/3334.400, WHD: 131x113x13 mm
