


Rittal – The System.

Faster – better – everywhere.



SK 3321.700

Chopped-fibre filter mat

State: 01.02.2026 (Source: rittal.com/ua-en)



FRIEDHELM LOH GROUP

SK 3321.700 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

Features

| | |
|-----------------------|--|
| Model No. | SK 3321.700 |
| Design | for filter fans |
| Product description | Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm. |
| Material | Chemical fibres |
| Note | Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats. |
| To fit Model No. | 3237.2xx/3237.1xx |
| Dimensions | Width: 89 mm Height: 89 mm Depth: 10 mm |
| Filter class | to DIN EN 779: G2 to DIN EN ISO 16890: ISO Coarse 50% |
| Packs of | 5 pc(s). |
| Net weight | 0.005 |
| Gross weight | 0.007 |
| Customs tariff number | 56039390 |
| EAN | 4028177184282 |
| E-Number Sweden | E3404732 |
| ETIM 9 | EC002513 |
| ETIM 8 | EC002513 |

Features

ECLASS 8.0

27180706

Approvals

Certificates

EAC