
## Rittal – The System.

Faster - better - everywhere.





# SV 3450.505 Conductor connection clamp

State: 04.11.2025 (Source: rittal.com/ua-en)



## SV 3450.505 - Conductor connection clamp Push-in

For the connection of round conductors.

#### **Features**

Model No.	SV 3450.505
Benefits	Maintenance-free Time-saving top-mounting Terminal box with integral label panels Universal conductor connection
Applications	For use as busbar pick-off of L, N or PE conductors in switchgear and controlgear, and as a conductor connection clamp in meter boxes.  For mounting on E-Cu or CUPONAL busbars
Function principle	Fully insulated terminal for tool-free conductor connection Conductor is released by the integral release pin
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7042
Test specification	IEC 60 999-1 IEC 60 947-7-1/-2
Connection of round conductors, fine wire with wire end ferrule	0.5 - 4 mm²
Connection of round conductors, fine wire without wire end ferrule	0.5 - 4 mm²
Connection of round conductors, multi-wire	0.5 - 4 mm²
Connection of round conductors, single-wire	0.5 - 6 mm²
For bar thickness	5 mm
Packs of	10 pc(s).
Net weight	0.14

© Rittal 2025

### Features

0.151
0.5 kg CO2 eq (Cat B)
Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
85369010
4028177813960
EC000001
EC000001
27141146

## **Approvals**

Approvals	ABS
	Lloyds Register of Shipping UR + C-UR (recognized)
Explanations	Declaration of conformity

© Rittal 2025 3