

Rittal – The System.

Faster – better – everywhere.



IT 3659.191

Server telescopic slides

State: 02.04.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 3659.191 - Server telescopic slides for IT rack systems and IT racks

Ensure optimum access to the servers, even when built-in. For servers with a maximum width of 430 mm.



Features

Model No.	IT 3659.191
Design	For 573.65 - 701.65 mm distance between levels
Product description	Ensure optimum access to the servers, even when built-in. For servers with a maximum width of 430 mm.
Material	Sheet steel
Load capacity	30 kg
Note	Only in conjunction with L-shaped mounting angles
To fit	Enclosure type: TS TS IT VX VX IT Depth: = 800 mm
Packs of	2 pc(s).
Net weight	2.82 kg
Gross weight	3.08 kg
PCF per pack (cradle-to-gate)	6 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared

Features

Customs tariff number	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Product description	Server telescopic slides for TS, TS IT, VX, VX IT, for depth 800 mm, extension piece: 573 mm, for servers max. 430 mm wide