

Rittal – The System.

Faster – better – everywhere.



HD 4000.083 Viewing window HD

State: 23.05.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.083 - Viewing window HD

For the protection of switches or displays.

Features

| | |
|-------------------------------------|---|
| Model No. | HD 4000.083 |
| Product description | For the protection of switches or displays. |
| Benefits | Large viewing panel Gap-free transition between the viewing window and the frame External hinge With T handle for easy opening without a key |
| Material | Frame: Stainless steel 1.4301 (AISI 304) Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 Viewing window: Polycarbonate |
| Supply includes | 2 hinges T handle Assembly parts |
| Visible area | Viewing window width: 400 mm Viewing window height: 330 mm |
| Dimensions | Width: 518 mm Height: 436 mm Depth: 65 mm |
| To fit | Enclosure type: HD compact enclosure |
| IP protection category to IEC 60529 | IP 55 |
| IK Code | IK08 |
| Installation options | For external mounting on surfaces. |
| Type rating to UL 50E | Type 1 Type 12 Type 13 |
| Packs of | 1 pc(s). |
| Net weight | 4.15 kg |

Features

| | |
|-----------------------|---|
| Gross weight | 4.206 kg |
| Customs tariff number | 39252000 |
| ETIM 9 | EC002527 |
| ETIM 8 | EC002527 |
| ECLASS 8.0 | 27182204 |
| Product description | HD System window, with T handle, WxH: 518x436 mm, stainless steel, 1.4301 |
