

Rittal – The System.

Faster – better – everywhere.



AS 4050.744 Wire end ferrules

State: 20.07.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.744 - Wire end ferrules loose

With plastic collar.



Features

Model No.	AS 4050.744
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Red
Length	8 mm
AWG	18
Internal diameter	3.5 mm
For cross-section	1 mm ²
DIN colour code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Delivery form	Loose
Packs of	500 pc(s).
Gross weight	0.5

Features

Customs tariff number	85369010
EAN	4028177805125
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------