## Rittal - The System.

Faster - better - everywhere.





# AS 4051.682 Wire end ferrules

State: 07.12.2025 (Source: rittal.com/ua-en)



### AS 4051.682 - Wire end ferrules loose

With plastic collar.

#### **Features**

Model No.	AS 4051.682
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	White
Length	10 mm
AWG	20
Internal diameter	2.9 mm
DIN colour code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Delivery form	Loose
Packs of	500 pc(s).
Net weight	0.5
Gross weight	0.041
Customs tariff number	85369010
EAN	4028177999596
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

© Rittal 2025

## Approvals

Approvals

UL + C-UL (listed)

UR

© Rittal 2025 3