

Rittal – The System.

Faster – better – everywhere.



AS 4054.000 Crimping pliers

State: 23.08.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.000 - Crimping pliers for wire end ferrules

For use with wire end ferrules with no insulating collar to DIN 46228 Part 1 and wire end ferrules with insulating collar to DIN 46228 Part 4.



Features

Model No.	AS 4054.000
Design	Angled
Product description	For use with wire end ferrules with no insulating collar to DIN 46228 Part 1 and wire end ferrules with insulating collar to DIN 46228 Part 4.
Benefits	Minimal effort required with large wire cross-sections Uniformly high quality compression Marked die stations for precise machining of the relevant cross-sections Releasable ratchet
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: Anthracite and Rittal Power Pink
Compression	Trapezoid crimp
Direction of cable entry	Side
Dimensions	Height: 59 mm Length: 198 mm
AWG	24 - 10
For cross-section	0.25 - 6 mm ²

Features

Packs of	1 pc(s).
Net weight	0.439
Gross weight	0.449
Customs tariff number	82032000
EAN	4028177807587
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811