

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.020 Crimping pliers

State: 14.07.2025 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.020 - Crimping pliers for ring terminals

For use with non-insulated ring terminals



## Features

Model No.	AS 4054.020
Design	Angled
Product description	For use with non-insulated ring terminals.
Benefits	Releasable ratchet Optimised lever transmission means that only minimal actuator forces are required, even with large cross-sections
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: Anthracite and Rittal Power Pink
Compression	Indent crimp
Dimensions	Height: 59 mm Length: 198 mm
AWG	20 - 14
For cross-section	0.5 - 2.5 mm <sup>2</sup>
Packs of	1 pc(s).
Net weight	0.429
Gross weight	0.439
Customs tariff number	82032000

# Features

EAN	4028177807624
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811