


# Rittal – The System.

Faster – better – everywhere.



## AS 4054.140 Crimping pliers

State: 29.08.2025 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.140 - Crimping pliers for ring terminals

For use with insulated ring terminals and connectors



## Features

|                     |   |
|---------------------|---|
| Model No.           | AS 4054.140   |
| Design              | Angled  |
| Product description | For use with insulated ring terminals and connectors.   |
| Benefits            | Clear allocation of cross-sections, thanks to colour coding on the dies<br>Releasable ratchet<br>Releases as soon as the required pressure is reached, to prevent underpressing |
| Material            | High-quality special tool steel   |
| Surface finish      | Matt, plated  |
| Colour              | Handle: Anthracite and Rittal Power Pink  |
| Compression         | Oval crimp  |
| Dimensions          | Height: 59 mm<br>Length: 198 mm   |
| AWG                 | 22 - 14   |
| For cross-section   | 0.75 - 2.5 mm <sup>2</sup>  |
| Packs of            | 1 pc(s).  |
| Net weight          | 0.42  |
| Gross weight        | 0.44  |

# Features

|                       |               |
|-----------------------|---------------|
| Customs tariff number | 82032000      |
| EAN                   | 4028177807686 |
| ETIM 9                | EC000168      |
| ETIM 8                | EC000168      |
| ECLASS 8.0            | 21043811      |