


**Faster – better – everywhere.**



AS 4055.473

Hole punch, sub-D

State: 24.06.2025 (Source: [rittal.com/ua-en](https://rittal.com/ua-en))



**ENCLOSURES**

## ► POWER DISTRIBUTION

## CLIMATE CONTROL

## IT INFRASTRUCTURE

## ► SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# AS 4055.473 - Hole punch, sub-D for sheet steel and stainless steel

For punching rectangular cut-outs for connectors

## Features

Model No.	AS 4055.473
Product description	For punching rectangular cut-outs for connectors. The hole punch is operated with a wrench or hydraulic punch.
Benefits	With side ejector for the waste No jamming of the die Anti-twist axles for stamps and dies are used as tension bolts.
Supply includes	Female dies Male dies Tension bolts Lock nut Pressure nut with ball bearing Adaptor for hydraulics Plastic case
Machinable material	Sheet steel Stainless steel
Maximum machinable material thickness, stainless steel	1.25 mm
Maximum machinable material thickness, sheet steel	1.75 mm
□ punch	58.4 x 11.3 mm
Packs of	1 pc(s).
Net weight	0.695
Gross weight	0.873
Customs tariff number	82073010
EAN	4028177808584

# Features

ECLASS 8.0

21049047