

# Rittal – The System.

Faster – better – everywhere.



## SZ 4139.300 Courtesy light

State: 24.05.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 4139.300 - Courtesy light

Supply voltage: 100 - 240 V AC 50/60 Hz

## Features

|  |   |
|--|---|
| Model No.  | SZ 4139.300   |
| Design   | without door operated switch  |
| Supply includes                                    | Courtesy light<br>Light<br>Light cover<br>Assembly parts  |
| Power consumption                                  | 30 W  |
| Ballast  | Wide-range electronic ballast   |
| Connection options                                 | Power supply via connectors<br>Door-operated switch<br>Through-wiring (creating rows of lights) |
| Light  | Fluorescent lamp, base G13  |
| Protection class                                   | I (PE conductor)  |
| Switch (type)                                      | Integral on/off/door-operated switch  |
| Light cover  | Yes   |
| Light – installation type                          | Screw-fastening   |
| Rated impulse withstand voltage,<br>phase to earth | 2000 V AC   |
| Rated impulse withstand voltage,<br>phase to phase | 1000 V AC   |
| Rated insulation voltage                           | 500 V DC/1s   |

# Features

---

|                             |   |
|-----------------------------|---|
| Installation options        | TS horizontal section of the roof frame: direct<br>TS, SE vertical section: with TS adaptor bracket<br>SE sections at the front and rear of the roof frame: with TS adaptor bracket<br>SE extrusions at the side of the roof frame: direct<br>AE, CM, TP: with universal bracket<br>AE: with rail for interior installation |
| Dimensions                  | Width: 987 mm<br>Height: 117 mm<br>Depth: 50 mm   |
| Operating temperature range | -15 °C...45 °C  |
| Sockets                     | D, earthing-pin (type F, CEE 7/4)   |
| Storage temperature range   | -20 °C...70 °C  |
| Rated operating voltage     | 100 V - 240 V, 1~, 50 Hz/60 Hz  |
| Socket version              | D, earthing-pin (type F, CEE 7/4)   |
| Packs of                    | 1 pc(s).  |
| Net weight                  | 2.15 kg   |
| Gross weight                | 2.3 kg  |
| Customs tariff number       | 94054990  |
| ECLASS 8.0                  | 27189241  |
| Product description         | SZ Courtesy light, WHD: 987x117x50 mm, 30 W, 100-240 V, 50/60 Hz, without door operated switch, with earthing-pin socket  |

---

# Approvals

---

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|