



# Rittal – The System.

Faster – better – everywhere.



## VX 5301.332

## Gland plate module, one-piece, with brush strip

State: 26.08.2025 (Source: [rittal.com/ua-en](https://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5301.332 - Gland plate module, one-piece, with brush strip for VX IT

For targeted cable entry from below.

## Features

Model No.	VX 5301.332
Design	one-piece, with brush strip
Product description	For targeted cable entry from below.
Material	Module plate: Sheet steel Brush strip: Plastic, UL 94 HB, halogen-free
Surface finish	Module plate: Zinc-plated
Supply includes	Assembly parts
Assembly instruction	Several gland module plates must be combined to seal the base completely in the VX IT The gland plate module may be combined in exchange with other base modules with a depth of 237.5 mm.
Note	Gland plate modules with brush strip not suitable for applications with a protection category to IEC 60 529
Dimensions	Depth: 237.5 mm
To fit	Enclosure type: VX IT Width: = 600 mm
Packs of	1 pc(s).
Net weight	1.14
Gross weight	1.34
PCF per pack (cradle-to-gate)	5.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177950849

# Features

---

ETIM 9	EC002620
--------	----------

---

ECLASS 8.0	27189261
------------	----------

## Tender text

VX IT Gland plate module, Art.-No. 5301.332,  
with brush strip, for cable routing  
For a rack width of 600 mm  
Depth: 237,5 mm  
For VX, VX IT  
For a cable entry over brushes  
Module plate: Sheet steel, zinc-plated  
Brush strip: UL 94-HB, halogen-free