


**Rittal – The System.**

Faster – better – everywhere.



**VX 5301.337**

**Gland plate set, multi-piece, solid**

State: 08.07.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5301.337 - Gland plate set, multi-piece, solid for VX IT

Multi-piece gland plate set consisting of solid base plate modules and a sliding panel for cable entry.

## Features

Model No.	VX 5301.337
Product description	Multi-piece gland plate set consisting of solid base plate modules and a sliding panel for cable entry. The solid gland plate module, depth 237.5 mm, may optionally be exchanged for gland plate module variants for cable entry.
Benefits	The sequence of individual modules may be freely selected
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Gland plate set Sealing tape Assembly parts 1 gland plate module, solid, depth: 75 mm 2 gland plate modules, solid, depth: 237.5 mm 1 sliding panel, depth: 115 mm
To fit	Enclosure type: VX IT Width: = 800 mm Depth: = 800 mm
Packs of	1 pc(s).
Net weight	6.42 kg
Gross weight	6.44 kg
PCF per pack (cradle-to-gate)	24.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261

# Features

---

Product description

VX IT gland plate module, multi-piece, solid, for width 800 mm, W x D 800 x 800 mm, sheet steel