


# Rittal – The System.

Faster – better – everywhere.



## DK 5301.571

## Sheet steel door, one-piece, vented

State: 28.05.2026 (Source: [rittal.com/ua-en](https://www.rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5301.571 - Sheet steel door, one-piece, vented for VX IT

To replace existing doors. The vented surface area is approx. 85% perforated.



## Features

Model No.	DK 5301.571
Product description	To replace existing doors. The vented surface area is approx. 85% perforated.
Material	Sheet steel
Surface finish	Spray-finished
Colour	Door: RAL 7035 Comfort handle VX: RAL 9005
Supply includes	Door with comfort handle for semi-cylinders with security lock 3524 E 3 x 130° hinges, fitted on the inside Assembly parts
Assembly instruction	For a door opening angle of 180° when baying, a 180° baying hinge is required
Note	Door opening angle for stand-alone siting: max. 165° Door opening angle when baying: max. 110°

# Features

To fit	Enclosure type: VX IT Width: = 800 mm Height: = 2,000 mm
Packs of	1 pc(s).
Net weight	13.4 kg
Gross weight	14.4 kg
PCF per pack (cradle-to-gate)	54.9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC000747
ECLASS 8.0	27182204
Product description	Sheet steel door, one-piece, ventilated for VX IT, to replace existing doors. The vented surface area is approx. 85% perforated. For enclosure width 800 mm, for enclosure height 2,000 mm