

Rittal – The System.

Faster – better – everywhere.



DK 5302.043

Cable tray, depth-variable

State: 23.05.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5302.043 - Cable tray, depth-variable for VX IT, TE 8000

For protected cable routing between the front and rear installation area.



Features

| | |
|---|--|
| Model No. | DK 5302.043 |
| Product description | For protected cable routing between the front and rear installation area. |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 9005 |
| Supply includes | Assembly parts |
| Installation options | Mounting angle system VX IT standard Mounting angle system TX CableNet TS IT mounting angle system |
| Mounting position of the 482.6 mm (19") level | VX IT Standard: min. 510 mm - max. 710 mm, with alternative attachment 415 mm - 615 mm TX CableNet: min. 510 mm - max. 710 mm, with alternative attachment 415 mm - 615 mm TS IT: min. 510 mm - max. 710 mm, with alternative attachment 415 mm - 615 mm |
| Length | 350: 550 mm |
| Packs of | 1 pc(s). |
| Net weight | 1.74 kg |
| Gross weight | 1.94 kg |

Features

| | |
|-------------------------------|--|
| PCF per pack (cradle-to-gate) | 7.4 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000322 |
| ECLASS 8.0 | 27400604 |
| Product description | IT cable tray, depth-variable, 350 – 550 mm, sheet steel, zinc-plated, RAL 9005 |