


**Rittal – The System.**

Faster – better – everywhere.



IT 5302.123

Mounting angles additional  
fastening attachment

State: 23.05.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# IT 5302.123 - Mounting angles additional fastening attachment for VX IT 482.6 mm (19") mounting angles, standard

Additional fastening attachment for mounting angles for VX IT to counteract unevenly distributed loads.

## Features

|                               |   |
|-------------------------------|---|
| Model No.                     | IT 5302.123   |
| Product description           | Prevents the mounting angles from twisting in case of unevenly distributed loads. Secured directly between the mounting angle and a mounting section on the outer mounting level of the VX frame structure. |
| Benefits                      | Can also be used as individual fastening with 482.6 mm (19") partial installation   |
| Applications                  | For fixing the 482.6 mm (19") mounting angle, standard, onto the outer mounting level   |
| Material                      | Sheet steel   |
| Surface finish                | Spray-finished  |
| Colour                        | RAL 9005  |
| Supply includes               | Assembly parts  |
| To fit                        | Width: = 600 mm   |
| Packs of                      | 2 pc(s).  |
| Net weight                    | 0.24 kg   |
| PCF per pack (cradle-to-gate) | 1 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared  |
| Customs tariff number         | 83024900  |
| ETIM 9                        | EC002625  |

# Features

---

ECLASS 8.0

27189234

---

Product description

Mounting angle additional fastening attachment, for VX IT 19"  
mounting angle standard, for fastening the 482.6 mm (19")  
mounting angle standard onto the outer mounting level, for  
enclosure width 600 mm