

Rittal – The System.

Faster – better – everywhere.



CP 6681.000 Premium Panel

State: 27.06.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6681.000 - Premium Panel Stainless steel

Premium Panel made of stainless steel 1.4301 (AISI 304), resistant to high-pressure cleaning.



Features

| | |
|-------------------------------------|---|
| Model No. | CP 6681.000 |
| Design | With support arm connection CP 40, stainless steel |
| Benefits | Resistant to high-pressure cleaning: The seal lies between two surfaces and is optimally compressed by the screw fastening. Suitable for clean room use: Screw fastening to comply with high standards in the food industry. With plastic stoppers on the inside or hex screws on the outside. |
| Material | Stainless steel 1.4301 (AISI 304) |
| Surface finish | Brushed, grain 400 |
| Dimensions | Width: 530 mm Height: 360 mm Depth: 120 mm |
| IP protection category to IEC 60529 | IP 66 IP X9 |
| To fit support arm connection | Top or bottom (by rotating the enclosure) |
| Cleanroom class | Air purity class 1 to DIN EN ISO 14 644-1 |
| Basic material | Stainless steel 1.4301 (AISI 304) |
| Packs of | 1 pc(s). |

Features

| | |
|-------------------------------|--|
| Net weight | 8.835 kg |
| Gross weight | 9.3 kg |
| PCF per pack (cradle-to-gate) | 35.41 |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002504 |
| ECLASS 8.0 | 27180505 |
| Product description | CP Premium Panel IP 69K, WHD: 530x360x120 mm, Stainless steel 1.4301, To fit panels WH 482.6x310 mm, Installation depth 115 mm |

Approvals

| | |
|--------------|--|
| Explanations | Declaration of conformity Declaration of conformity UK PCF-declaration |
|--------------|--|