

# Rittal – The System.

Faster – better – everywhere.



## IW 6900.740 Industrial Workstations

State: 06.09.2025 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# IW 6900.740 - Industrial Workstations

Lower enclosure section, based on VX SE for Industrial Workstations.



## Features

Model No.	IW 6900.740
Design	Worktop, keyboard drawer, designer door, rear door
Material	Enclosure, keyboard drawer, designer door and rear door: Sheet steel Worktop: Chipboard (plastic-laminated on both sides (edging))
Surface finish	Enclosure: Dipcoat-primed, powder-coated on the outside, textured paint
Colour	Decorative trim panels: RAL 7015
Supply includes	Enclosure sealed at the sides Three-piece gland plates Levelling feet Worktop, keyboard drawer, designer door, rear door Worktop, W x H x D 610 x 38 x 645 mm
Dimensions	Width: 600 mm Height: 1,000 mm Depth: 645 mm
IP protection category to IEC 60529	IP 54

# Features

Dimensions with worktop	Width: 610 mm Height: 1,043 mm Depth: 645 mm
Packs of	1 pc(s).
Net weight	71
Gross weight	74
PCF per pack (cradle-to-gate)	281.9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
EAN	4028177968547
ETIM 9	EC002502
ETIM 8	EC002502
ECLASS 8.0	27180501

# Approvals

Certificates	Surface finish
Explanations	Declaration of conformity Declaration of conformity UK