

Rittal – The System.

Faster – better – everywhere.



DK 7072.240

Nylon loop

State: 17.04.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7072.240 - Nylon loop

With the nylon loop, secured cables are easily released, allowing individual cables to be added or removed, ideal for sensitive data cables (fibre-optic/Cu).

Features

| | |
|-----------------------|---|
| Model No. | DK 7072.240 |
| Product description | With the nylon loop, secured cables are easily released, allowing individual cables to be added or removed. Ideal for sensitive data cables (fibre-optic/Cu), as it avoids indentations on the cable sheathing. In addition, the nylon loop may be screw-fastened to the round system punchings or attached using a quick-release fastener. |
| Colour | Black |
| Supply includes | Quick-release fastener |
| Dimensions | Width: 20 mm Length: 300 mm |
| Max. cable diameter | 90 mm |
| Packs of | 10 pc(s). |
| Net weight | 0.04 kg |
| Gross weight | 0.054 kg |
| Customs tariff number | 39191019 |
| ETIM 9 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | DK Nylon loop, WxL: 20x300 mm, For Ø: 90 mm |

Tender text

Nylon loop for cable routing, max. cable diameter 90 mm

The nylon loop is attached to cable clamp rails, C rails, system rails or to the enclosure frame. The nylon loop may be screw-fastened as per the 25 mm DIN pitch pattern. The nylon loop can hold cable bunches up to 90 mm in diameter; single cables can easily be added or detached.

Nylon loop length: 300 mm

Max. cable diameter: 90 mm

Packs of 1