

Rittal – The System.

Faster – better – everywhere.



DK 7178.535 Patch panel

State: 19.12.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7178.535 - Patch panel for fibre-optic splicing box, lockable

There are 5 different fibre-optic panels available for various coupling types. The number of locations per panel varies depending on the chosen variant and basic size of the panel.

Features

Model No.	DK 7178.535
Product description	For splicing boxes, there is a choice of multiple panels with corresponding cut-outs for the installation of single or duplex fibre-optic couplings.
Material	Sheet steel
Colour	RAL 7035
Number of locations	20
for fibre-optic coupling	E-2000 E-2000 duplex SC LC LC duplex
Note on Model No.	For E-2000 duplex only half of the locations are available.
Units	1 U
Packs of	1 pc(s).
Net weight	0.25
Gross weight	0.302
PCF per pack (cradle-to-gate)	1.2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177166851
ETIM 9	EC001129

Features

ECLASS 8.0

19170113

Tender text

Patch panel for fibre-optic splicing box, 1 U

For installing 20 European 2000 SC couplings or 10 E 2000 duplex couplings including fixtures for holding the cable clamping devices.

Version: sheet steel

Surface finish: RAL 7035