Rittal - The System.

Faster – better – everywhere.





State: 11.12.2025 (Source: rittal.com/ua-en)



DK 7391.000 - Data Rack

Data Rack for optimum accessibility from all sides during assembly and installation as well as extensive mobility when using twin castors.







Features

Model No.	DK 7391.000
	אט 1.000
Material	Profile frame, base/plinth: Sheet steel
	Feet: Die-cast zinc
General colour	RAL 7035
Colour	Profile frame, base/plinth: RAL 7035
	Trim panel, feet: RAL 5018
Supply includes	Torsionally stiff profile frame with 482.6 mm (19") punchings
	Stable base/plinth with integral feet, with the option of floor
	anchoring without base trim panels
	Mounting accessories
Dimensions	Width: 550 mm
	Height: 1,500 mm
	Depth: 750 mm
Units	31 U
Units	31 U
Distance from the second	150 - 350 mm
mounting level, 50 mm pitch	
pattern	

© Rittal 2025

Features

Pitch pattern between the mounting levels	50 mm
Load capacity of the 482.6 mm (19") mounting angles	1,500 N
Note	Order second mounting level separately
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	16.781
Gross weight	17.664
PCF per pack (cradle-to-gate)	67.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight approximately calculated and self-declared
Customs tariff number	94032080
EAN	4028177129795
E-Number Sweden	E7239646
ETIM 9	EC002507
ECLASS 8.0	27180602

© Rittal 2025 3

Tender text

482.6 mm (19 inch) rack, 31 U

Torsionally stiff frame section, welded from 2 mm sheet steel, with integral 482.6 mm (19 inch) punchings and round and square holes in the 25 mm DIN pitch pattern for accommodation of cabling systems and 482.6 mm (19 inch) components.

The rack is depth-adjustable in a pitch pattern of 50 mm on a folded sheet steel base/plinth with die-cast zinc feet. The base/plinth can accommodate a second 482.6 mm (19 inch) mounting level, offers the option of floor anchoring and fastening facilities for levelling feet and castors.

Infinitely bayable.

Material: Sheet steel Colour: RAL 7035

Dimensions: Rack height 1500 mm, 31 U,

base/plinth: WxD: 550 x 750 mm

© Rittal 2025 4